



V. Guldmann A/S
Graham Bells Vej 21-23A
DK-8200 Aarhus N
Tel. +45 8741 3100
Fax +45 8741 3131
info@guldmann.com
www.guldmann.com

GH Positioning Lock Technical specifications

Function

Usage : To lock GH3+ hoist and traverse rail
in a certain position

Weight

Lock : 3 x 1,4 kg

Materials

Lock function : Rustproof and galvanized steel
Covers : Impact-resistant UL 94 V-0 flame
retardant recyclable plastic

Electronics

On/off : Automatic when used.
Power supply : 33 V AC, 2.5 A
Supply voltage,
transformer : 115/230 V AC
Battery : 1 x 24V NiMH
Max charge time : 2 hours

Measurements


A : 120 mm
B : 150 mm
C : 70 mm
D : min. 10 mm clearance

Markings

The product is manufactured in compliance with the Council Directive 93/42/EEC of June 14th 1993, including amendments, as medical device class 1.

Item Number/Model

557600 : GH Positioning Lock



Time to care